


MVF90 Series flow

Time in seconds to evacuate to vacuum level (Sec/1000L)

Model	Vacuum levels (-kPa)									
	0	10	20	30	40	50	60	70	80	90
MVF90-10	0	19	50	110	246	430	690	1100	1870	4288
MVF90-20	0	14	36	79	176	307	493	786	1336	3063
MVF90-30	0	9	24	52	117	205	329	524	890	2042
MVF90-40	0	7	18	39	88	154	246	393	668	1531



Vacuum flow at different vacuum levels (L/Min)

Model	Vacuum levels (-kPa)									
	0	10	20	30	40	50	60	70	80	90
MVF90-10	355	205	133	65	46	36	24	14	6	0
MVF90-20	513	287	186	91	64	50	34	20	8	0
MVF90-30	690	431	279	137	97	76	50	29	13	0
MVF90-40	994	574	372	182	129	101	67	39	17	0

